

Variants:

- ...X053M - for M ports (see the picture I and the table below);
- ...X053G - for G ports (see the picture I and the table below);
- ...X053U - for U ports (see the picture I and the table below).

I - variants


Variant M



Variant G



Variant U (SAEJ475 (ISO R725))



Type	Displacement cm ³ /rev	Flow		Pressure P _{nom} bar	max Speed n rpm	Dimension							
		at 1500 rpm V _{min}	at max rpm V _{min}			Inlet			Outlet				
						A mm	B mm	M	G	U	M	G	U
ZRP-X11-11	1	1,40	3,26	250	3500	39,1	81						
ZRP-X11-14	1,25	1,74	4,07	250	3500	39,5	82						
ZRP-X11-19	1,6	2,23	5,21	250	3500	40,3	83,6						
ZRP-X11-24	2	2,82	6,58	250	3500	41,1	85,2						
	2,5	3,53	8,23	250	3500	42,1	87,2						
	2,65	3,74	8,72	250	3500	42,4	87,8						
ZRP-X11-36	3,15	4,44	10,36	250	3500	43,5	89,8						
ZRP-X11-44	3,65	5,15	12,01	250	3500	44,4	91,9						
ZRP-X11-48	4,2	5,92	13,82	250	3500	45,5	94,1						
	4,7	6,63	15,46	250	3500	46,1	96						
	5	7,05	14,10	250	3000	47,1	97,2						
ZRP-X11-60	5,7	8,12	16,25	200	3000	48,5	100,1						
ZRP-X11-70	6,1	8,69	14,49	200	2500	49,4	101,8						
	7,4	10,55	17,58	180	2500	52,1	107,2						
	8	11,40	15,20	150	2000	53,4	109,7						
	8,5	12,11	16,15	150	2000	54,4	111,7						
	9,8	13,97	18,62	120	2000	57	117						

* - These pumps - only under a special order